

Nano SPY T2

Mini Temperature Data logger 2,4GHz radiofrequency communication



on contractual phot

Presentation

The Nano SPY T2 measures and records temperature with its external probe. It transmits the data to a nearby LINK module via 2.4 GHz radio frequency communication.

The data are then automatically sent to the JRI secure Cloud for hosting, and will be managed from the JRI MySirius web application.

If thresholds are exceeded, alerts are transmitted in real time to react immediately.

Designed to monitor thermo-controlled chambers, the sensor can be fixed thanks to its magnet outside of the equipment.

Technical features

	Standard Version	Incubator Version
Interface	Status LED and On/Off touch sensitve button	
Measurement range	-50°C to +105°C	
Accuracy	$\pm 0.3^{\circ}$ C from -20°C to +30°C and $\pm 0.5^{\circ}$ C out of this range	$\pm 0.2^{\circ}$ C from $+30^{\circ}$ C to $+50^{\circ}$ C and $\pm 0.5^{\circ}$ C out of this range
Communication frequency	2,4 GHz (802.15.4)	
Memory	10 000 data points	
Temperature sensor	External PT100 probe - Ø5x20mm	
Operating conditions	-30°C to +70°C	
Resolution	0.01	
Measuring and transmission frequency	Adjustable from 5 sec to 12 hrs	
Recording frequency (internal memory)	Adjustable from 5 sec to 24 hrs	
Response time	~2 mn at 90% of the variation	
Protection	IP65	
Case	Polycarbonate – Food contact	
Dimensions and weight	63 x 42 x 25 mm / ~ 60 g	
Cable lenght	30 cm, 3m or 8m	30 cm or 3m
Power supply	3,6v Lithium battery - Replaceable	
Battery life	2 to 4 years depending on use	
Fixation	Fixing eyelets and integrated magnets	
Supplied with	Blue JRI identification ring	Yellow identification ring
	Battery, user manual can be download on www.jri-maxant.com	
Compliance	CE, ROHS, FCC, ETS 300-328, EN 12830	
Standard calibration points	-18°C/+6°C/+22°C	+36°C/+38°C/+45°C

JRI, Société par actions simplifiée au capital de 4 000 000 €

Pôle logistique / 2 Rue de la Voivre / PA Technoland / BP 21 / 25490 FESCHES LE CHÂTEL / France SIRET 380 332 858 00030 - Tél : +33 (0)3 8130 68 04 / Fax : +33 (0)3 8130 60 99 / sales@jri.fr

Benefits

Easy-to-use

The sensor is ready to use and has operating and alarm lights



Excellent measurement accuracy



Fixing eyelets



Replaceable battery and non disconnectable probe



Incubator Version

PART NRS 11569 : Nano SPY T2 30cm 11570 : Nano SPY T2 3m 11571 : Nano SPY T2 8m 11569_! : Nano SPY T2 30cm 11570_! : Nano SPY T2 3m